


# EYE WASH AND SAFETY SHOWERS



10

## **Combination Safety Shower with Hand Operated**



Creative CESS7



10592:1982

### **Technical Specification :**

- Shower Heads: ABS.
- Eye Wash Basin: ABS.
- Eye Wash Atomiser Unit: ABS
- Pipe & Pipe fittings: Galvanized 'C' class heavy duty ISI marked.
- ½" Valve: SS 304
- 1" Valve: SS 304
- Push plate: ABS.
- Flange: MS.
- Stay open valve design: keeps the users hands free to hold eyes open in case of chemical splash.
- Recommended Water pressure: 28 LPM for Eye Wash.
- 110 LPM for Combination and Shower.
- Recommended water pressure : 2kg/cm<sup>2</sup>.
- Bureau of Indian Standards approved ISI 10592:1982

## **Combination Safety Shower with Foot Pedal**



Creative CESS8



10592:1982

### **Technical Specification :**

- Shower Heads:ABS.
- Creative Eye Wash Basin: ABS.
- Creative Eye Wash Atomiser Unit: ABS
- Pipe & Pipe fittings: Galvanized 'C' class heavy duty ISI marked.
- ½" Valve: SS 304
- 1" Valve : SS 304
- Foot pedal: Aluminium casting.
- Flange: MS.
- Stay open valve design: keeps the users hands free to hold eyes open in case of chemical splash.
- Recommended Water pressure: 28 LPM for Eye Wash.
- 110 LPM for Combination and Shower.
- Recommended water pressure : 2kg/cm<sup>2</sup>.
- Bureau of Indian Standards approved ISI 10592:1982

## **Combination Safety Shower with Hand Operated (SS)**



Creative CSE7-SS304



### **Technical Specification :**

- Shower Heads: SS 304.
- Eye Wash Basin: SS 304.
- Eye Wash Atomiser Unit: SS 304.
- Pipe & Pipe fittings: SS 304.
- ½" Valve: SS 304
- 1" Valve: SS 304
- Push plate: SS 304.
- Flange: SS 304.
- Stay open valve design: keeps the users hands free to hold eyes open in case of chemical splash.
- Recommended Water pressure: 28 LPM for Eye Wash.
- 110 LPM for Combination and Shower.
- Recommended water pressure : 2kg/cm<sup>2</sup>.
- Bureau of Indian Standards approved ISI 10592:1982

## **Combination Safety Shower with Foot Pedal (SS)**



Creative CSE8-SS304



### **Technical Specification :**

- Shower Heads: SS304
- Creative Eye Wash Basin: SS304
- Creative Eye Wash Atomiser Unit: SS304
- Pipe & Pipe fittings: SS304
- 1/2" Valve: SS 304
- 1" Valve SS 304
- Foot pedal: SS304
- Flange: SS304
- Stay open valve design: keeps the users hands free to hold eyes open in case of chemical splash.
- Recommended Water pressure: 28 LPM for Eye Wash. 110 LPM for Combination and Shower.
- Recommended water pressure: 2kg/cm<sup>2</sup>.

## Emergency Eye/Face Wash Fountain



Creative CSE1



### **Technical Specification :**

- Eye Wash Basin: Injection ABS.
- Eye Wash Atomiser Unit: ABS
- Pipe & Pipe fittings: Galvanized 'C' class heavy duty ISI marked.
- ½" valve: SS 304.
- Flange: MS.
- Stay open valve design: keeps the users hands free to hold eyes open in case of chemical splash.
- Recommended Water pressure: 28 LPM
- Recommended water pressure : 2kg/cm2.

## Emergency Eye/Face Wash Fountain with Foot Pedal



Creative CSE2



### **Technical Specification :**

- Eye Wash Basin: Injection ABS.
- Eye Wash Atomiser Unit: ABS
- Pipe & Pipe fittings: Galvanized 'C' class heavy duty ISI marked.
- ½" valve: SS 304.
- Foot pedal : Aluminium casting.
- Flange: MS.
- Stay open valve design: keeps the users hands free to hold eyes open in case of chemical splash.
- Recommended Water pressure: 28 LPM
- Recommended water pressure : 2kg/cm2.

## Emergency Eye/Face Wash Fountain (SS)



Creative CSE1-SS304



### **Technical Specification :**

- Eye Wash Basin: Injection SS 304.
- Eye Wash Atomiser Unit: SS 304.
- Pipe & Pipe fittings: SS 304.
- ½" valve: SS 304.
- Flange: SS 304.
- Stay open valve design: keeps the users hands free to hold eyes open in case of chemical splash.
- Recommended Water pressure: 28 LPM
- Recommended water pressure : 2kg/cm2.
- Bureau of Indian Standards approved ISI 10592:1982

## Eye-Wash Bottle



Creative CEB13

### Technical Specification :

- Creative Emergency Eye-Wash Bottle manufactured out of soft food grade plastic ensures steady soft flow of potable water to the injured ocular area helping to flush away the acid/alkali contaminant preventing any further injury to the eye.
- Creative Emergency eye wash bottle has an eye cup with a snap fit cap.
- The air vent valve provided prevents the contaminated fluid from entering the bottle again.
- Portable, Light Weight and Easy to use at any work place.

## Creative Eye / Face Wash Push Lever operated, wall mounted



Creative CSE1B



10592:1982

### Technical Specification :

- Eye-Wash Basin: ABS
- Atomizer Unit: ABS
- Pipe and Pipe Fittings: GI 'C' Class heavy duty IS marked
- ½" Valve: SS 304
- Push Plate: ABS
- Wall Stand: MS
- Recommended Water Pressure: 2 Kg/Cm2
- Recommended Water Flow: 28 LPM

## Portable Eye Wash Shower



Creative CEPEW12

### Technical Specification :

- Portable Eye Wash Unit Station
- Portable gravity operated eyewash features a 10-gallon capacity, FDA high-density polyethylene tank that provides for over 15 minutes of full pattern flushing at 0.4 gpm.
- Pulling the yellow activation Arm down to the open position activates unit. Tank has handle on top to allow easy handling. A wide-fill opening with threaded cap permits easy inspection, cleaning and filling.
- Model supplied with wall bracket and bacteriostatic additive to permit storage of water for up to six months.



Scan QR code to  
download catalogues

## MARK SAFETY APPLIANCES



**Regd. Office, Warehouse & Workshop:**

Plot No. 92, 93, Shah Industrial Park-3 at Kotambi,  
Pin Code 391510, Vadodara-Halol Highway,  
Dist. Vadodara, Gujarat, India.



02668 299065



info@marksafety.com



www.marksafety.com

Connect us:

